# Hand Tools

# RZR Series Cable Shears

## 1253105

- For cutting copper and aluminium cables
- Not suitable for steel wire and wire ropes

Forged in Germany




| CODE NO | mm / " | Ø mm | |
|---|---|---|---|
| 1253105 | 170 - 6-1/2" | 15 | 6 |

## 1253109

**Bent Long Nose Pliers**
(Polished Finish/DuoTech Handles)
DIN / TS ISO 5745

Suitable for cutting soft and hard wire, special tool steel, polished finish (electrofilmed), softgrip handles

| CODE NO | mm / " | Ø mm | |
|---|---|---|---|
| 1253109 | 200 - 8" | 1.6 | 6 |

## 12531 Series

**Water Pump Pliers**
(Box Joint/PVC Sleeves)
DIN ISO 8976

9-position adjustment, box-joint design, Chrome Vanadium steel, phosphate finish, PVC sleeves

| CODE NO | mm / " | Ø max. mm | |
|---|---|---|---|
| 1253103 | 250 - 10" | 28 | 6 |
| 1253104 | 300 - 12" | 35 | 6 |

## 1253101

**6 Piece Screwdriver Set- Slotted/Phillips**

| CODE NO | |
|---|---|
| 1253101 | 1 |

| | | |
|---|---|---|
| | Slotted | 3.0x75, 4.0x100, 5.5x125, 6.5x150 mm |
| | Phillips | PH1x80, PH2x100 mm |

## 1253102

**6 Piece Screwdriver Set - Slotted/Pozidriv**

| CODE NO | |
|---|---|
| 1253102 | 1 |

| | | |
|---|---|---|
| | Slotted | 3.0x75, 4.0x100, 5.5x125, 6.5x150 mm |
| | Pozidriv | PZ1x80, PZ2x100 mm |

## 12530 Series
**Insulated Slotted Screwdrivers**
(VDE Approved)

VDE 0682 Teil 201, DIN ISO 2380

1000 V EN 60900

For live working up to 1000V AC or 1500V DC, Chrome Vanadium Molybdenum steel blade (phosphate finish), softgrip handle

**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | mm | mm | |
|---|---|---|---|
| 1253078 | 2.5 | 75 | 12 |
| 1253079 | 3.0 | 100 | 12 |
| 1253080 | 3.5 | 100 | 12 |
| 1253081 | 4.0 | 100 | 12 |
| 1253082 | 5.5 | 125 | 12 |
| 1253083 | 6.5 | 150 | 12 |

## 12530 Series
**Insulated Phillips Screwdrivers**
(VDE Approved)

VDE 0682 Teil 201, DIN ISO 8764

1000 V EN 60900

For live working up to 1000V AC or 1500V DC, Chrome Vanadium Molybdenum steel blade (phosphate finish), softgrip handle

**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | | mm | |
|---|---|---|---|
| 1253084 | PH1 | 80 | 12 |
| 1253085 | PH2 | 100 | 12 |

## 12530 Series
**Insulated Pozidriv Screwdrivers**
(VDE Approved)

VDE 0682 Teil 201, DIN ISO 8764

1000 V EN 60900

For live working up to 1000V AC or 1500V DC, Chrome Vanadium Molybdenum steel blade (phosphate finish), softgrip handle

**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | | mm | |
|---|---|---|---|
| 1253086 | PZ1 | 80 | 12 |
| 1253087 | PZ2 | 100 | 12 |

## 12530 Series
**Insulated Terminal (Pozidriv/Slotted) Screwdrivers** (VDE Approved)

VDE 0682 Teil 201, DIN ISO 8764

1000 V EN 60900

For terminal screws (Pozidriv/Slotted), ideal for live working up to 1000V AC or 1500V DC, Chrome Vanadium Molybdenum steel blade (phosphate finish), softgrip handle

**Individually tested as per DIN EN 60900: 2004 norm**

| CODE NO | | mm | |
|---|---|---|---|
| 1253088 | MOD1 | 80 | 12 |
| 1253089 | MOD2 | 100 | 12 |

## 12530 Series
**Insulated Combination Pliers**
(VDE Approved)

VDE 0682 Teil 201, DIN ISO 5746

1000 V EN 60900

Ideal for live working up to 1000V AC or 1500V DC, suitable for cutting soft and hard wire, special tool steel, chrome finish, softgrip handles

**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | mm / " | Ø mm | |
|---|---|---|---|
| 1253065 | 160 - 6" | 1.8 | 6 |
| 1253066 | 180 - 7" | 2.0 | 6 |
| 1253067 | 200 - 8" | 2.5 | 6 |

## 12530 Series
**Insulated Diagonal Cutters**
(VDE Approved)

VDE 0682 Teil 201, DIN ISO 5749

1000 V EN 60900

Ideal for live working up to 1000V AC or 1500V DC, suitable for cutting soft and hard wire, special tool steel, chrome finish, softgrip handles

**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | mm / " | Ø mm | |
|---|---|---|---|
| 1253068 | 140 - 5-1/2" | 1.8 | 6 |
| 1253069 | 160 - 6" | 2.0 | 6 |
| 1253070 | 180 - 7" | 2.5 | 6 |

## 1253071
**Insulated Power Diagonal Cutters**
(VDE Approved)

VDE 0682 Teil 201, DIN ISO 5749

1000 V EN 60900

Ideal for live working up to 1000V AC or 1500V DC, suitable for cutting all wires (incl. piano wire), special tool steel, chrome finish, softgrip handles

**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | mm / " | Ø mm | |
|---|---|---|---|
| 1253071 | 180 - 7" | 2.0 | 6 |

## 12530 Series
**Insulated Long Nose Pliers**
(VDE Approved)

VDE 0682 Teil 201, DIN ISO 5745

1000 V EN 60900

Ideal for live working up to 1000V AC or 1500V DC, suitable for cutting soft and hard wire, special tool steel, chrome finish, softgrip handles

**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | mm / " | Ø mm | |
|---|---|---|---|
| 1253072 | 160 - 6" | 1.6 | 6 |
| 1253073 | 200 - 8" | 1.6 | 6 |

## 1253074
**Insulated Bent Long Nose Pliers**
(VDE Approved)

VDE 0682 Teil 201, DIN ISO 5745

1000 V EN 60900

Ideal for live working up to 1000V AC or 1500V DC, suitable for cutting soft and hard wire, special tool steel, chrome finish, softgrip handles

**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | mm / " | Ø mm | |
|---|---|---|---|
| 1253074 | 200 - 8" | 1.6 | 6 |

## 1253075
**Insulated Wire Stripping Pliers**
(VDE Approved)
VDE 0682 Teil 201

1000 V EN 60900

Ideal for live working up to 1000V AC or 1500V DC, for stripping the plastic insulation of single and multi-strand conductors, special tool steel, chrome finish, softgrip handles
**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | mm / " | mm² | |
|---|---|---|---|
| 1253075 | 160 - 6" | 10 | 6 |

## 1253076
**Insulated Water Pump Pliers**
VDE 0682 Teil 201, DIN ISO 8976

1000 V EN 60900

Ideal for live working up to 1000V AC or 1500V DC, 9-position adjustment, box-joint design, Chrome Vanadium steel, phosphate finish, softgrip handles
**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | mm / " | ∅ max. mm | |
|---|---|---|---|
| 1253076 | 250 - 10" | 28 | 6 |

## 1253077
**RZR Series Insulated Cable Shears**
(VDE Approved)

1000 V EN 60900

Ideal for live working up to 1000V AC or 1500V DC, for cutting copper and aluminum cables, special tool steel, phosphate finish, softgrip handles
Not suitable for steel wire and wire ropes
**Individually tested as per DIN EN 60900: 2012 norm**

| CODE NO | mm / " | ∅ mm | |
|---|---|---|---|
| 1253077 | 170 - 6-1/2" | 15 | 6 |

## 1253094
**2 Piece Insulated Pliers Set** (VDE Approved)

1000 V EN 60900

| CODE NO | |
|---|---|
| 1253094 | 1 |

180 mm Combination Pliers
160 mm Diagonal Cutters

## 1253095
**3 Piece Insulated Pliers Set** (VDE Approved)

1000 V EN 60900

| CODE NO | |
|---|---|
| 1253095 | 1 |

180 mm Combination Pliers
160 mm Diagonal Cutters
160 mm Long Nose Pliers

## 1253096
**5 Piece Insulated Pliers and Screwdriver Sets**
(VDE Approved)

1000 V EN 60900

| CODE NO | |
|---|---|
| 1253096 | 1 |

180 mm Combination Pliers
160 mm Diagonal Cutters
Slotted 4x100, 5.5x125 mm
Pozidriv PZ2x100 mm

## 12530 Series
**9 Piece Insulated Pliers and Screwdriver Sets**
(VDE Approved-in Vinyl Wallet)

1000 V EN 60900

| CODE NO | |
|---|---|
| 1253097 | 1 |

180 mm Combination Pliers
160 mm Diagonal Cutters
160 mm Long Nose Pliers
Slotted 2.5x75, 4x100, 5.5x125 mm
Phillips PH1x80 mm, PH2x100 mm
Voltage Tester, Long

| | |
|---|---|
| 1253098 | 1 |

180 mm Combination Pliers
160 mm Diagonal Cutters
160 mm Long Nose Pliers
Slotted 2.5x75, 4x100, 5.5x125 mm
Pozidriv PZ1x80, PZ2x100 mm
Voltage Tester, Long



COLD IMPACT RESISTANCE (-25°C)




ELECTRICAL TEST (10.000V)




PRESSURE TEST (5000V)




INSULATION ADHESION TEST



FLAMMABILITY TEST




10.000V TEST (%100 Control)

## 12530 Series

**12 Piece Insulated Pliers and Screwdriver Sets** (VDE Approved-in Vinyl Wallet)

1000 V EN 60900

| CODE NO | |
|---|---|
| 1253099 | 1 |

- 180 mm Combination Pliers
- 160 mm Diagonal Cutters
- 160 mm Long Nose Pliers
- Automatic Wire Stripper
- Slotted 2.5x75, 4x100, 5.5x125 mm
- Phillips PH1x80, PH2x100 mm
- Voltage Tester, Long
- Trimming Knife Trapezoid Blade 19 mm
- Compact Tape Measures 3mx16mm

| | |
|---|---|
| 1253100 | 1 |

- 180 mm Combination
- 160 mm Diagonal Cutters
- 160 mm Long Nose Pliers
- Automatic Wire Stripper
- Slotted 2.5x75, 4x100, 5.5x125 mm
- Pozidriv PH1x80, PH2x100 mm
- Voltage Tester, Long
- Trimming Knife Trapezoid Blade 19 mm
- Compact Tape Measures 3m x 16mm

## 1253092

**4 Piece Insulated Screwdriver Set** (VDE Approved) - **Slotted/Phillips**

1000 V EN 60900

x3

x1

| CODE NO | |
|---|---|
| 1253092 | 1 |

- Slotted 2.5x75, 4.0x100, 5.5x125,
- Phillips PH2x100 mm

## 1253093

**4 Piece Insulated Screwdriver Set** (VDE Approved) - **Slotted/Pozidriv**

1000 V EN 60900

x3

x1

| CODE NO | |
|---|---|
| 1253093 | 1 |

- Slotted 2.5x75, 4.0x100, 5.5x125 mm
- Phillips PZ2x100 mm

## 12530 Series

**Rethreading Tools**

For cleaning out and cutting damaged threads in electrical boxes, precision ground HSS tap, softgrip handle

| CODE NO | M SIZE | mm | |
|---|---|---|---|
| 1253090 | M3.5x0.6 | 118 | 12 |
| 1253091 | M4.0x0.7 | 118 | 12 |

## 1253106

**6 Piece Electronics Screwdriver Set - Slotted/Phillips**

x4

x2

| CODE NO | |
|---|---|
| 1253106 | 1 |

- Slotted 1.5x40, 2.0x60, 2.5x80, 3.0x80 mm
- Phillips PH00x60, PH0x60 mm

## 1253108

**6 Piece Electronics Screwdriver Set - TORX**

x6

| CODE NO | |
|---|---|
| H99-04-06 | 1 |

- Torx T5x40, T6x40, T7x40, T8x40, T9x60, T10x60

## 1253107

**6 Piece Electronics Screwdriver Set - Slotted/Phillips**

x4

x2

| CODE NO | |
|---|---|
| 1253107 | 1 |

- Slotted 1.5x40, 2.0x60, 2.5x80, 3.0x80 mm
- Phillips PH00x60, PH0x60 mm

# Hand Tools